

# Bar

Description		Spec				Qty	
X	2011-T3 Rd. Bar	QQA-225/3	0.5		144	3	8.5
X	2011 AL T3 rd. bar	QQA-225/3	3		11	1	7.8
X	2011-T3 Sq bar	QQA-225/3	0.5	0.5	47.75	1	1.2
	2014-T651 Rd. Bar	QQA-225/4	0.75		144.25	1	6.4
X	2014-T651 Rd. Bar	QQA-225/4	0.875		24.25	1	1.5
	2014-T651 Rd. Bar	QQA-225/4	1		24.25	1	1.9
	2014-T651 Rd. Bar	QQA-225/4	2		11.875	1	3.8
X	2024-T351 Rd. Bar ( T-4)	QQA-225/6	0.5		144	5	14.2
	2024-T351 Rd. Bar	QQA-225/6	0.5		131.88	1	2.6
	2024-T351 Rd. Bar	QQA-225/6	0.63		12	1	0.4
X	2024-T351 Rd. Bar	QQA-225/6	0.625		144	3	13.3
X	2024-T351 Rd. Bar	QQA-225/6	0.75		59.75	1	4.7
X	2024-T351 Rd. Bar	QQA-225/6	1		35.5" & 43.75"	2	6.2
	2024-T351 Rd. Bar	QQA-225/6	1.25		63.75	1	7.9
X	2024-T351 Rd. Bar	QQA-225/6	1.875		12	1	3.3
X	2024-T3511 Rd. Bar	QQA-200/3	0.38		71.5	1	0.8
X	2024-T3511 Rd. Bar	QQA-200/3	0.5		144	1	2.8
X	2024-T3511 Rd. Bar	QQA-200/3	0.5		23	1	0.5
	2024-T3511 rd. bar	QQA-200/3	1.25		36	1	4.4
X	2024-T3511 Rd. Bar	QQA-200/3	2.75		96	1	57.3
X	2024-T3511 rd. bar	QQA-200/3	4	4.5	114	1	144.1

	2024-T351 Flat Bar	QQA-225/6	0.375	1	72	1	2.7
X	2024-T351 Flat Bar	QQA-225/6	0.5	1.5	48	1	3.6
	2024-T351 Flat Bar	QQA-225/6	0.5	2.5	23	1	2.9
X	2024-T351 Flat Bar	QQA-225/6	0.5	1	23	1	1.2
	2024-T351 Flat Bar	QQA-225/6	0.5	5	95	1	23.8
	2024-T351 Flat Bar	QQA-225/6	0.5	6	11	1	3.3
X	2024-T351 Flat Bar	QQA-225/6	0.75	1.5	25.5	4	11.5

X	2024-T3511 Rect. Bar	QQA-200/3	0.25	1.25	11.5	1	0.4
X	2024-T3511 Rect. Bar	QQA-200/3	0.375	1	71.625	1	2.7
X	2024-T3511 Rect. Bar	QQA-200/3	0.75	1	144	1	10.8
X	2024-T3511 Rect. Bar	QQA-200/3	0.75	1	23.25	1	1.7
X	2024-T3511 Rect. Bar	QQA-200/3	1	1.75	144	1	25.2
	2024-T3511 Rect. Bar	ASTM-B221	2.5	2.75	24	1	16.5
X	2024-T3511 Rect. Bar	QQA-200/3	2.5	7	22.25	1	38.9
X	2024-T3511 Rect. Bar	QQA-200/3	2.5	2.25	36	1	20.3
X	2024-T3511 Rect. Bar	QQA-200/3	2.5	3	11.25	1	8.4
	2024-T3511 Rect. Bar	QQA-200/3F	2.5	2.75	42	1	28.9
X	2024-T3511 Rect. Bar	QQA-200/3	2.5	3	48	1	36.0
X	2024-T3511 Rect. Bar	QQA-200/3	3	1.25	72	1	27.0
X	2024-T3511 Rect. Bar	QQA-200/3	4	6	72	1	346.2
X	2024-T3511 Rect. Bar	QQA-200/3	4	6	10.25	1	28.8

X	2024-T351 Rect. Bar	QQA-225/6	0.375	3	83.25	1	9.4
X	2024-T351 Rect. Bar	QQA-225/6	0.375	3	36	1	4.1
X	2024-T351 Rect. Bar	QQA-225/6	0.375	6	47.25	1	10.6
X	2024-T351 Rect. Bar	QQA-225/6	2	2	30.625	1	12.3

	2024-T351 Sq. Bar	QQA-225/6	0.5	0.5	95	1	2.4
	2024-T351 Sq. Bar	QQA-225/6	0.5	0.5	72	1	1.8
	2024-T351 Sq. Bar	QQA-225/6	0.5	0.5	59.75	1	1.5
X	2024-T351 Sq. Bar	QQA-225/6	0.5	0.75	144	1	5.4
X	2024-T351 Sq. Bar	QQA-225/6	0.5	0.75	23.625	1	0.9
X	2024-T351 Rect. Bar	QQA-225/6	0.625	1	43.75	1	2.7
	2024-T351 Sq. Bar	QQA-225/6	0.63	0.63	48	1	1.9

	2024-T351 Rect. Bar	QQA-225/6	0.75	0.5	137.75	1	5.2
X	2024-T351 Rect. Bar	QQA-225/6	1	1.5	23.75	1	3.6
X	2024-T351 Rect. Bar	QQA-225/6	2	6	14.25	1	17.1
X	2024-T3511 Sq. Bar	QQA-200/3	0.75	0.75	35.75	1	2.0
X	2024-T3511 Sq. Bar	QQA-200/3	1	1	41.5	1	4.2
X	2024-T3511 Sq. Bar	QQA-200/3	1.25	1.25	47	1	7.3
	2024-T3511 Sq. Bar	QQA-200/3	1.25	1.25	65	1	10.2
X	2024-T3511 Sq. Bar	QQA-200/3	1.25	1.25	45.25	1	7.1
X	2024-T3511 Sq. Bar	QQA-200/3	2	2	22	1	8.8
	2024-T3511 Sq. Bar	QQA-200/3	4	4	70.75	1	113.2
X	2024-T4 SQ BAR	QQA-225/6	0.25	0.25	144	2	3.6
X	2024-T4 SQ BAR	QQA-225/6	0.25	0.25	84.875	1	0.5
	2024-T4 Rd. Bar	QQA-225/6	0.125		107	1	0.1
	2024-T4 Rd. Bar	QQA-225/6	0.125		144	3	0.5
X	2024-T4 Rd. Bar	QQA-225/6	0.188		144	6	2.4
	2024-T4 Rd. Bar	QQA-225/6	0.25		144	8	5.7
X	2024-T4 Rd. Bar	QQA-225/6	0.25		144	4	2.8
	2024-T4 Rd. Bar	QQA-225/6	0.25		144	3	2.1
	2024-T4 Rd. Bar	QQA-225/6	0.312		95.75	1	0.7
X	2024-T4 Rd. Bar	QQA-225/6	0.38		144	9	14.8
X	2024-T4 Rd. Bar	QQA-225/6	0.38		45	1	0.5
x20	2024-T4 Hex Bar	QQA-225/6	.500 HEX		14.25	4	
x	2024-T4 Hex Bar	QQA-225/6	.500 HEX		35.875	2	
X	2024-T4 Hex Bar	QQA-225/6	.500 HEX		35"	1	
	2024-T4 Flat Bar	QQA-225/6	0.188	1.5	71.5	1	2.0
X	2024-T4 Flat Bar	QQA-225/6	0.25	0.5	120	1	1.5
X	2024-T4 Flat Bar	QQA-225/6	0.25	0.5	11.88	1	0.1

X	2024-T4 Flat Bar	QQA-225/6	0.25	0.5	12	1	0.2
X	2024-T4 Flat Bar	QQA-225/6	0.313	2	120	1	7.5
	2024-T4 Flat Bar	QQA-225/6	0.38	1	38.5	1	1.5
	2024-T4 Flat Bar	QQA-225/6	0.375	1	71.75	1	2.6
	2024-T4 Flat Bar	QQA-225/6	0.375	2.25	60.125	1	5.1
	2024-T4 Flat Bar	QQA-225/6	1	0.75	119.75	1	9.0
	2024-T4 Flat Bar	QQA-225/6	0.375	2	144	1	10.8
X		QQA-225/6	0.312	2	47	1	2.9
X	2024-T4 Flat Bar	QQA-225/6	0.312	2	10	1	0.6
	2024-T4 Flat Bar	QQA-225/6	0.125	0.5	144.25	2	1.8
X	2024-T351 Rd. Bar	QQA-200/3	1		27.5	1	2.2
X	2024-T351 Rd. Bar	QQA-200/3	1		49	1	3.9
	2024-T851 Rd. Bar	QQA-225/6	2.75		96	1	57.4
	2024-T851 Sq. Bar	QQA-225/6	2	2	24	4	38.4
X	2219-T6	AMS-QQ-A-250/30	2.187	2.187	14	1	6.7
X	2219-T8511 Rd. Bar	AMS-4162D	0.375		144	4	6.3
X	2219-T8511 Rd. Bar	AMS-4162D	1		10.5	1	0.8
X	2219-T8511 RD BAR Consignment p/t	ASTM-B221-06	1		28.5	1	10.1
X	2219-T8511 Rd. Bar	ASTM-B221-06	1.25		11.5	1	1.4
X	2219-T8511 Rd. Bar	ASTM-B221-06	1.25		11.5	1	1.4
	2219-T855 Rd. Bar		5.5		5	1	11.9

X	5083-H32 Rect. Bar		2.5	3.75	11.625	1	10.9	
X								
X	5053-H111 RD BAR	ASTM-B221	2.75		98	1	58.5	
X	5053-H111 RD BAR	ASTM-B221	2.75		144	1	86.0	
	5086 Rd. Bar	QQA-200/5	0.25		71.38	1	0.4	
	5086 Rd. Bar	QQA-200/5	0.375		96	1	1.1	
	5086 Rd. Bar	QQA-200/5	0.375		43	2	1.0	
X	5086-H111 RD Bar	QQA-200/5	0.75		95.75	1	4.3	
X	5086-H111 RD Bar	QQA-200/5	1.75		72	1	17.4	
X	5086-H111 RD Bar	QQA-200/5	1.75		51.75	1	12.5	
	5086-H111 Rd. Bar	QQA-200/5	0.375		96	1	1.1	
	5086-H111 Rd. Bar	QQA-200/5	0.375		48	1	0.5	
	5086-H111 Flat Bar	QQA-200/5	0.38	4	155.875	1	23.7	
	5086-H111 Flat Bar	QQA-200/5	0.5	3	36	1	5.4	
	5086-H116 Flat Bar	QQA-200/5	0.38	5	11	1	2.1	
X	5454-H111 Flat Bar	QQA-200/5	0.19	1.5	95.75	1	2.7	
	5456-H111 Rd. Bar	QQA-200/7	1		23.63	1	1.9	
	5456-H111 Rd. Bar	QQA-200/7	1		72	1	5.7	
	5456-H111 Rd. Bar	QQA-200/7	1.25		72	1	8.9	
	5456-H111 Rd. Bar	QQA-200/7	1.25		47.63	1	5.9	
	6061-0 Rd. Bar	QQA-225/8A	0.25		72.13	1	0.4	
	6061-0 Rd. Bar	QQA-225/8A	0.25		71.88	1	0.4	

6061-0 Rd. Bar	QQA-200/8	0.5	41	1	0.8
----------------	-----------	-----	----	---	-----

X	6061-T6 Rd. Bar	ASTM-B211	0.125	144	4	0.7
X	6061-T6 Rd. Bar	ASTM-B211	0.187	131.75	1	0.4
X	6061-T6 Rd. Bar	ASTM-B211	0.19	65.5	1	0.2
X	6061-T6 Rd. Bar	ASTM-B211	0.19	144	1	0.4
X	6061-T6 Rd. Bar	ASTM-B211	0.25	144	23	16.4
X	6061-T6 Rd. Bar	ASTM-B211	0.3125	108	1	0.8
X	6061-T6 Rd. Bar	ASTM-B211	0.375	95.75	1	1.1
	6061-T6 Rd. Bar	ASTM-B211	0.38	71.63	1	0.8
X	6061-T6 Rd. Bar	ASTM-B211	0.38	133.75	1	1.5
X	6061-T6 Rd. Bar	ASTM-B211	0.38	95.88	1	1.1
X	6061-T6 Rd. Bar	ASTM-B211	0.38	63.5	1	0.7
	6061-T6 Rd. Bar	ASTM-B211	0.5	31.25	1	0.6
X	6061-T6 Rd. Bar	ASTM-B211	0.5	51	1	1.0
X	6061-T6 Rd. Bar	ASTM-B211	0.5	23.5	2	0.9
X	6061-T6 Rd. Bar	ASTM-B211	0.5	19.5	1	0.4
X	6061-T6 Rd. Bar	ASTM-B211	0.5	72	1	1.4
X	6061-T6 Rd. Bar	ASTM-B211	0.5	144	1	2.8
X	6061-T6 Rd. Bar	ASTM-B211	0.562	131.875	1	3.3
X	6061-T6 Rd. Bar	ASTM-B211	0.562	144	4	14.4
X	6061-T6 Rd. Bar	ASTM-B211	0.625	73	1	2.3
X	6061-T6 Rd. Bar	ASTM-B211	0.6875	50.5	1	1.9
X	6061-T6 Rd. Bar	ASTM-B211	0.6875	144	1	5.4
X	6061-T6 Rd. Bar	ASTM-B211	0.6875	38.25	1	1.4
X	6061-T6 Rd. Bar	ASTM-B211	0.75	60	2	5.3
X	6061-T6 Rd. Bar	ASTM-B211	0.75	9.5	1	0.4
X	6061-T6 Rd. Bar	ASTM-B211	0.75	11.6875	2	1.0
X	6061-T6 Rd. Bar	ASTM-B211	0.75	59.75	1	2.7
X	6061-T6 Rd. Bar	ASTM-B211	0.75	144	1	6.4
X	6061-T6 Rd. Bar	ASTM-B211	0.875	39.25	1	2.4
X	6061-T6 Rd. Bar	ASTM-B211	1	18.25	1	1.4
X	6061-T6 Rd. Bar	ASTM-B211	1	47.5	1	3.8
X	6061-T6 Rd. Bar	ASTM-B211	1	24	1	1.9
X	6061-T6 Rd. Bar	ASTM-B211	1	60	2	9.5

X	6061-T6 Rd. Bar	ASTM-B211	1		35	1	2.8
X	6061-T6 Rd. Bar	ASTM-B211	1		23.75	1	1.9
X	6061-T6 Rd. Bar	ASTM-B211	1.125		136.3125	1	13.6
X	6061-T6 Rd. Bar	ASTM-B211	1.25		35	1	4.3
X	6061-T6 Rd. Bar	ASTM-B211	1.25		36	1	4.4
X	6061-T6 Rd. Bar	ASTM-B211	1.25		12	1	1.5
X	6061-T6 Rd. Bar	ASTM-B211	1.25		144	1	17.8
X	6061-T6 Rd. Bar	ASTM-B211	1.38		83.5	1	12.6
X	6061-T6 Rd. Bar	ASTM-B211	1.5		27.25	1	4.8
X	6061-T6 Rd. Bar	ASTM-B211	1.5		72.25	1	12.8
X	6061-T6 Rd. Bar	ASTM-B211	1.5		72.13	1	12.8
X	6061-T6 Rd. Bar	ASTM-B211	1.625		6	1	1.3
X	6061-T6 Rd. Bar	ASTM-B211	1.6875		144	8	259.2
X	6061-T6 Rd. Bar	AMS-QQA-250/8 ASTM-B211	1.75		133.5	1	32.2
X	6061-T6 Rd. Bar	ASTM-B221	2		48.13	1	15.2
X	6061-T6 Rd. Bar	ASTM-B211	2		17.75	1	5.6
X	6061-T6 Rd. Bar	ASTM-B211	2		23.9375	1	9.5
X	6061-T6 Rd. Bar	ASTM-B221	2		16.625	1	5.3
X	6061-T6 Rd. Bar	ASTM-B221	2 DIA		48	1	15.0
X	6061-T6 Rd. Bar	ASTM-B211	2.5		144	4	284.4
X	6061-T6 Rd. Bar	ASTM-B211	2.5		35	1	17.3
X	6061-T6 Rd. Bar	ASTM-B211	2.5		108	2	106.7
X	6061-T6 Rd. Bar	ASTM-B211	2.625		39.75	1.0	21.6
X	6061-T6 Rd. Bar	ASTM-B211	2.75		103	1	61.5
x	6061-T6 Rd. Bar	AMS-A225/8 ASTM-AB211	3 DIA		6.5	1	12.0
X	6061-T6 Rd. Bar	ASTM-B211	3.25		73.25	1	61.1
X	6061-T6 Rd. Bar	ASTM-B211	3.75		7.5	1	8.3
X	6061-T6 Rd. Bar	ASTM-B211	6		9.5	1	27.0
X	6061-T6 Rd. Bar machined	AMS-QQ-A-367-1, ASTM-B247	9.75		14	1	105.1
X	6061-T6 Rd. Bar	AMS-QQ-A-367-1, ASTM-B247	9.875		14.25	1	109.8
X	6061-T6 Rd. Bar	AMS-QQ-A-367-1, ASTM-B247	10		14.125	1	111.6

	AMS-QQA-200/8 ASTM-B221	0.75		128	1	5.7
X	6061-T6 Hex. Bar					
	6061-T6 Rd. Bar	ASTM-B221	0.25	11.38	1	0.1
X	6061-T6 Rd. Bar	ASTM-B221	0.38	71.88	1	0.8
	6061-T6 Rd. Bar	ASTM-B221	0.4375	50.875	1	0.8
	6061-T6 Rd. Bar	ASTM-B221	0.4375	144	1	2.2
	6061-T6 Rd. Bar	ASTM-B221	0.5	60	1	1.2
	6061-T6 Rd. Bar	ASTM-B221	0.5	11.75	1	0.2
	6061-T6 Rd. Bar	ASTM-B221	0.5	48	1	0.9
	6061-T6 Rd. Bar	ASTM-B221	0.5	49.75	1	1.0
	6061-T6 Rd. Bar	AMS-QQA-200/8 ASTM-B221	0.5	144	1	2.8
X	6061-T6 Rd. Bar	AMS-QQA-200/8 ASTM-B221	0.5	40	1	0.8
X	6061-T6 Rd. Bar	ASTM-B221	0.5	144	2	5.7
	6061-T6 Rd. Bar	ASTM-B221	0.5	144.125	1	2.8
X	6061-T6 Rd. Bar	ASTM-B221	0.5	144	7	19.9
X	6061-T6 Rd. Bar	ASTM-B221	0.625	23.625	1	0.7
	6061-T6 Rd. Bar	ASTM-B221	0.875	84	1	5.1
X	6061-T6 Rd. Bar	ASTM-B221	1	102	1	8.1
X	6061-T6 Rd. Bar	ASTM-B221	1	23.875	1	1.8
X	6061-T6 Rd. Bar	ASTM-B221	1	71.75	1	5.7
X	6061-T6 Rd. Bar	ASTM-B221	1	36	1	2.8
X	6061-T6511 ( conform to T6)	ASTM-B221	1.25	35.75	1	14.0
X	6061-T6 Rd. Bar	ASTM-B221	1.25	23	1	2.8
X	6061-T6 Rd. Bar	ASTM-B221	1.25	83.875	1	10.4
X	6061-T6 Rd. Bar	ASTM-B221	1.25	9	1	1.1
X	6061-T6 Rd. Bar	ASTM-B221	1.25	71.5	1	8.8
X	6061-T6 Rd. Bar	ASTM-B221	1.25	47.25	1	5.8
X	6061-T6 Rd. Bar	ASTM-B221	1.38	19.75	1	3.0
X	6061-T6 Rd. Bar	ASTM-B221	1.375	11.75	1	1.8
	6061-T6 Rd. Bar	ASTM-B221	1.38	71.88	1	10.8
X	6061-T6 Rd. Bar	ASTM-B221	1.5	47.625	1	8.5
X	6061-T6 Rd. Bar	ASTM-B221	1.5	48	1	34.1
X	6061-T6 Rd. Bar	ASTM-B221	1.75	27.75	1	6.7
X	6061-T6 Rd. Bar	ASTM-B221	1.75	97.75	1	23.6
	6061-T6 Rd. Bar	ASTM-B221	2	59.5	1	18.8
X	6061-T6 Rd. Bar	ASTM-B221	2	23.875	9	67.9
X	6061-T6 Rd. Bar	ASTM-B221	2	35.5	1	11.2

X	6061-T6 Rd. Bar	ASTM-B221	2		21.5	1	6.8
X	6061-T6 Rd. Bar	ASTM-B221	2.125		12.75	1	4.5
X	6061-T6 Rd. Bar	ASTM-B221	3		7.75	1	5.5
X	6061-T6 Rd. Bar	ASTM-B221	4.5		8.5	1	13.6
X	6061-T6 Rd. Bar	ASTM-B221	9.75		15	2	225.3
X	6061-T6 Rd. Bar	ASTM-B221	10		12.125	1	95.8
X	6061-T6 Rd. Bar	QQA-367A	10		20	1	158.0

X	6061-T6 Flat Bar	ASTM-B221	0.125	0.75	72	1	0.7
	6061-T6 Flat Bar	ASTM-B221	0.13	0.5	71	1	0.5
	6061-T6 Flat Bar	ASTM-B221	0.187	4	37.13	1	2.8
	6061-T6 Flat Bar	ASTM-B221	0.19	0.5	48	2	0.9
	6061-T6 Flat Bar	ASTM-B221	0.25	0.75	59.25	1	1.1
X	6061-T6 Flat Bar	ASTM-B221	0.25	1	11	1	0.3
	6061-T6 Flat Bar	ASTM-B221	0.25	1.5	59	1	2.2
X	6061-T6 Flat Bar	ASTM-B221	0.25	3	71.9375	1	5.4
X	6061-T6 Flat Bar (made from rect tube)	AMS-QQA-200/8	0.25	3	157.5	2	23.6
X	6061-T6 Flat Bar	ASTM-B221	0.25	3	47.875	1	3.6
	6061-T6 Flat Bar	ASTM-B221	0.25	6	9	1	1.4
	6061-T6 Flat Bar	ASTM-B221	0.312	3	63	1	5.9
X	6061-T6 Flat Bar	ASTM-B221	0.375	1	36	1	1.4
X	6061-T6 Flat Bar	ASTM-B221	0.375	0.5	48	1	0.9
X	6061-T6 Flat Bar	ASTM-B221	0.375	1	35.75	7	9.4
X	6061-T6 Flat Bar	ASTM-B221	0.375	4	47.875	1	7.2
	6061-T6 Flat Bar	ASTM-B221	0.375	1	36	1	1.4
X	6061-T6 Flat Bar	ASTM-B221	0.375	2	28	1	2.1
X	6061-T6 Flat Bar	ASTM-B221	0.375	1	144	1	5.4
X	6061-T6 Flat Bar	ASTM-B221	0.375	5	24	1	4.5
	6061-T6 Flat Bar	ASTM-B221	0.38	0.5	60	1	1.1
X	6061-T6 Flat Bar	ASTM-B221	0.38	0.5	12.13	12	2.8
X	6061-T6 Flat Bar	ASTM-B221	0.38	0.5	35.75	12	8.2
X	6061-T6 Flat Bar	ASTM-B221	0.5	3	23.875	2	7.2
	6061-T6 Flat Bar	ASTM-B221	0.5	7	25.88	1	9.1
X	6061-T6 Flat Bar	ASTM-B221	0.5	1	72	1	3.6
X	6061-T6 Flat Bar	ASTM-B221	0.5	2	48.75	1	4.9
	6061-T6 Flat Bar	ASTM-B221	0.5	2.5	32	1	4.0
X	6061-T6 Flat Bar	ASTM-B221	0.5	4	27.5	2	11.0

X	6061-T6 Flat Bar	ASTM-B221	0.625	1.25	52.5	1	4.1
X	6061-T6 Flat Bar	ASTM-B221	0.625	8	23.625	1	11.8
	6061-T6 Flat Bar	ASTM-B221	0.63	8	48.38	1	24.4
X	6061-T6 Flat Bar	ASTM-B221	0.75	1	132.13	1	9.9
X	6061-T6 Flat Bar	ASTM-B221	0.75	1.25	83	1	7.8
X	6061-T6 Flat Bar	ASTM-B221	0.75	1.25	119.5	1	11.2
X	6061-T6 Flat Bar	ASTM-B221	0.75	1.5	72	1	8.1
X	6061-T6 Flat Bar	ASTM-B221	0.75	1.5	100	1	11.3
X	6061-T6 Flat Bar	ASTM-B221	0.75	4	35.5	2	21.3
X	6061-T6 Flat Bar	ASTM-B221	0.75	1.5	41.5	1	4.7
X	6061-T6 Flat Bar	ASTM-B221	0.75	8	144	2	172.8
X	6061-T6 Flat Bar	ASTM-B221	0.875	1.445	36.125	1	4.6
X	6061-T6 Flat Bar	ASTM-B221	1	1.25	12	1	1.5
X	6061-T6 Flat Bar	ASTM-B211	1	1.5	119	1	17.9
X	6061-T6 Flat Bar	ASTM-B221	1	2	8.75	1	1.8
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1	6	56.75	1	34.0
X	6061-T6 Flat Bar	ASTM-B221	1	6	18.125	1	10.9
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1	1.75	47.875	1	8.3
X	6061-T6 Flat Bar	ASTM-B221	1	1.75	36	1	6.3
X	6061-T6 Flat Bar	ASTM-B221	1	2	119.875	1	24.0
X	6061-T6 Flat Bar	ASTM-B221	1.25	2.25	18	1	5.1
X	6061-T6 Flat Bar	ASTM-B221	1.5	2.5	144	1	54.0
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1.5	5	108	1	81.0
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1.5	5	27.75	1	20.8
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1.5	8	67.75	1	81.3
X	6061-T6 Flat Bar	ASTM-B221	1.5	1.75	10	1	2.6
X	6061-T6 Flat Bar	ASTM-B221	1.5	3.5	12	1	6.3
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	0.25	1	144	1	3.6
	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	1.63	2	40.75	1	13.3
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	2	7	47	1	65.8
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	2.5	3	31.375	1	23.5
	6061-T6 Flat Bar	ASTM-B221	3	4.75	12	1	17.1
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	3	4	19.875	2	47.7
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	3.25	7.75	12	1	30.2
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	3.5	4	8.75	1	12.3
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	3.5	4	26.75	1	37.5
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	3.5	4	51.5	3	216.3
X	6061-T6 Flat Bar	AMS-QQA-200/8 ASTM B221	4	8	12	1	38.4

X	6061-T6 Rect. Bar	AMS-QQA225/8 CF See Teri	0.5	2	24.25	1	2.4
X	6061-T6 Rect. Bar	ASTM-B211	0.75	1.5	47.625	1	5.4
X	6061-T6 Sq. Bar	ASTM-B221	0.25	0.5	59.5	1	0.7
X	6061-T6 Sq. Bar	ASTM-B221	0.38	0.5	107.75	1	2.0
X	6061-T6 Sq. Bar	ASTM-B221	0.38	0.5	100.63	1	1.9
X	6061-T6 Sq. Bar	ASTM-B221	0.38	0.5	95.75	1	1.8
X	6061-T6 Sq. Bar	ASTM-B221	0.38	0.5	35.625	1	0.7
X	6061-T6 Sq. Bar	ASTM-B221	0.38	0.38	47.5	1	0.7
X	6061-T6 Sq. Bar	ASTM-B221	0.5	0.5	47.88	1	1.2
X	6061-T6 Sq. Bar	ASTM-B221	0.5	0.05	47.625	1	0.1
X	6061-T6 Sq. Bar	ASTM-B221	0.75	0.75	31	1	1.7
X	6061-T6 Sq. Bar	ASTM-B221	0.75	0.75	131.875	1	7.4
X	6061-T6 Sq. Bar	ASTM-B221	0.88	0.88	23.75	1	1.8
X	6061-T6 Sq. Bar	ASTM-B221	1	1	68.75	1	6.8
X	6061-T6 Sq. Bar	ASTM-B221	1	1	13.75	1	1.4
X	6061-T6 Sq. Bar	ASTM-B221	1	1	15.5	1	1.6
X	6061-T6 Sq. Bar	ASTM-B221	1	1	47.75	1	4.8
X	6061-T6 Sq. Bar	ASTM-B221	1	1	47.625	1	4.8
X	6061-T6 Sq. Bar	ASTM-B221	1.25	1.25	108	1	16.8
X	6061-T6 Sq. Bar	ASTM-B221	1.25	1.25	48	4	30.0
X	6061-T6 Sq. Bar	ASTM-B221	1.5	1.5	47	1	10.6
X	6061-T6 Sq. Bar	ASTM-B221	1.5	3	119.75	1	53.9
X	6061-T6 Sq. Bar	ASTM-B221	1.5	1.5	144	1	32.4
X	6061-T6511 Sq. Bar	ASTM-B221	2.5	2.5	36	1	22.5
X	6061-T6511 Sq. Bar	ASTM-B221	2.5	2.5	8.375	1	5.2
X	6061-T6511 Sq. Bar	ASTM-B221	2.5	2.5	12	1	7.5
X	6061-T6511 Sq. Bar	ASTM-B221	4	4	95.5	1	152.8
X	6061-T6511 Sq. Bar	ASTM-B221	4	4	16	1	25.6
X	6061-T6511 Sq. Bar	ASTM-B221	6	6	47.75	1	171.9
X	6061-T6 Rd. Bar	AMS-QQA-250/11	10.4375		6	1	51.6
X	6061-T6511 HEX BAR	ASTM-B211	0.25		71.625	1	0.4
X	6061-T6511 HEX BAR	ASTM-B211	0.375		120.25	1	1.3

X	6061-T6511 HEX BAR	AMS-QQA-200/8 ASTM-B221	.500 HEX		119	1	2.0
X	6061-T6511 HEX BAR	ASTM-B211	0.75		128	1	5.7
X	6061-T6511 HEX BAR	ASTM-B221	1"		72	1	0.0
X	6063-T52 Rd. Bar	QQA-200/9	0.375		167.75	1	1.9
X	6063-T52 Rd. Bar	QQA-200/9	0.5		23.75	2	0.9
X	6063-T52 Rd. Bar	QQA-200/9	0.625		96	2	5.9
X	6063-T52 Rd. Bar	QQA-200/9	1.5		161.625	1	28.7
X	6063-T52 Rd. Bar	QQA-200/9	1.5		156	1	27.7
X	6063-T52 Rd. Bar	QQA-200/9	2		185	1	58.5
X	6063-F Rd. Bar	QQA-200/9	4		72	2	182.0
X	6063-T52 Sq. Bar	QQA-200/9	0.5	1.5	48	8	28.8
X	6063-T52 Sq. Bar	QQA-200/9	1	1	121	1	12.1
X	6063-T52 Sq. Bar	QQA-200/9	1.5	1.5	82.625	1	18.6
X	6063-T52 Rect. Bar	QQA-200/9	0.25	4.5	192	1	21.6
X	6063-T52 Rect. Bar	QQA-200/9	0.25	4.5	48	2	10.8
	6063-T52 Rect. Bar	QQA-200/9	0.75	1.5	119.63	1	13.5
	6063-T52 Rect. Bar	QQA-200/9	0.75	1.75	47.63	1	6.3
X	6063-T52 Rect. Bar	QQA-200/9	1.25	2.375	32.5	1	9.6
X	6063-T52 Rect. Bar	QQA-200/9	0.5	2	48	12	57.6
	6063-T52 Rect. Bar	QQA-200/9	0.5	8	144	3	172.8
X	6063-T52 Rect. Bar	QQA-200/9	0.25	3	51.63	1	3.9
X	6063-T52 Rect. Bar	QQA-200/9	0.25	3	58.38	1	4.4
X	6063-T52 Rect. Bar	QQA-200/9	0.25	3	107.13	1	8.0
	6063-T52 Rect. Bar	QQA-200/9	0.38	3	48.25	1	5.5

X	6063-T52 Rect. Bar	QQA-200/9	0.25	6	83.375	1	12.5
	6063-T52 Rect. Bar	QQA-200/9	0.5	8	72	1	28.8
	6063-T52 Rect. Bar	QQA-200/9	0.5	8	144	5	288.0
X	6063-T52 Rect. Bar	QQA-200/9	0.63	1	14.625	1	0.9
X	6063-T52 Rect. Bar	QQA-200/9	0.63	1	47.625	1	3.0
X	6063-T52 Rect. Bar	QQA-200/9	1.25	4	95.75	1	47.8
X	6063-T52 Rect. Bar	QQA-200/9	1.25	1.5	48	1	9.0
X	6063-T52 Rect. Bar	QQA-200/9	1.25	4	144	18	1296.0
X	6063-T6 Rect. Bar	QQA-200/3, 200/8, 200/9, 200/11	0.75	4	51.25	1	15.4
X	7075-0 RECT BAR	QQA-225/9	1	1.5	124	1	18.6
X	7075-T3511 Rd. Bar	QQA-200/11	1.5		68.75	1	
X	7075-T651 Rd. Bar	QQA-225/9	0.625		22.25	1	0.7
	7075-T651 Rd. Bar	QQA-225/9	0.75		144	1	6.4
	7075-T651 Rd. Bar	QQA-225/9	0.75		108	1	4.8
	7075-T651 Rd. Bar	QQA-225/9	0.75		12	1	0.5
X	7075-T651 Rd. Bar	QQA-225/9	1		48.13	3	11.4
X	7075-T651 Rd. Bar	QQA-225/9	1.25		71.88	1	8.9
X	7075-T651 Rd. Bar	QQA-225/9	1.875		60	1	16.7
X	7075-T651 Rd. Bar	QQA-225/9	1.875		11.75	1	3.3
X	7075-T651 Rd. Bar	QQA-225/9	1.875		84	1	23.3
	7075-T651 Rd. Bar	QQA-225/9	1.875		144.125	1	40.0
X	7075-T651 Rd. Bar	QQA-225/9	2.25		29.75	1	11.9
X	7075-T651 Rd. Bar	QQA-225/9	3.5		10.5	1	10.1
X	7075-T6511 Rd. Bar	QQA-200/11	0.375		59.75	1	0.7
X	7075-T6511 Rd. Bar	QQA-200/11	0.375		23.675	1	0.3

X	7075-T6511 Rd. Bar	QQA-200/11	0.375		103.38	1	1.1
X	7075-T6511 Rd. Bar	QQA-200/11	0.375		23.75	1	0.2
X	7075-T6511 Rd. Bar	QQA-200/11	0.5		23.63	1	0.5
X	7075-T651 Rd. Bar	QQA-200/11	0.75		131.5	1	5.8
X	7075-T6511 Rd. Bar	QQA-200/11	0.75		95.625	1	4.2
X	7075-T6511 Rd. Bar	QQA-200/11	0.75		144	1	6.4
	7075-T6511 Rd. Bar	QQA-200/11	0.88		75.5	1	4.6
X	7075-T651 Rd. Bar	QQA-200/11	1.5		60.25	1	10.7
X	7075-T6511 Rd. Bar	QQA-200/11	3		11.625	1	8.3
X	7075-T651 Rd. Bar	QQA-200/11	4.5		60	1	96.0
X	7075-T651 Rd. Bar	QQA-200/11	4.5		144	1	230.4
X	7075-T6511 Rd. Bar	QQA-200/11	4.5		83.5	1	133.6

	7075-T651 Rect. Bar	QQA-225/9	0.25	1.38	59.5	1	2.1
	7075-T651 Rect. Bar	QQA-225/9	0.38	1.5	119.88	1	6.8
	7075-T651 Sq. Bar	QQA-225/9	0.5	0.5	144	1	3.6
	7075-T651 Sq. Bar	QQA-225/9	0.75	0.75	35.88	1	2.0
X	7075-T6511 Rect. Bar	QQA-225/9	0.75	2	72	1	10.8
X	7075-T6511 Rect. Bar	QQA-225/9	0.75	2	59.75	1	9.0
	7075-T651 Rect. Bar	QQA-225/9	1	2.5	12	1	3.0
X	7075-T651 Rect. Bar	QQA-225/9	1.25	1.5	96	1	18.0
X	7075-T651 Rect. Bar	QQA-225/9	1.25	3	29.875	1	11.2
	7075-T651 Rect. Bar	QQA-225/9	1.25	6	23.625	1	17.7
X	7075-T651 Rect. Bar	QQA-225/9	1.25	2	50.63	1	12.7
X	7075-T651 Rect. Bar	QQA-225/9	1.5	2.5	14.25	1	5.3

X	7075-T6511 Rect. Bar	QQA-200/11	0.063	0.5	84	1	0.3
X	7075-T6511 Rect. Bar	QQA-200/11	0.25	1	11.875	1	0.3
X	7075-T6511 Rect. Bar	QQA-200/11	0.25	1	35.5	1	0.9
X	7075-T651 Rect. Bar	QQA-200/11	0.375	1.5	23.75	1	1.3
X	7075-T651 Rect. Bar	QQA-200/11	0.375	1	11	1	0.4
X	7075-T6511 Rect. Bar	QQA-200/11	0.375	1	22	1	0.8
X	7075-T6511 Rect. Bar	QQA-200/11	0.375	1	24	1	0.9

X	7075-T6511 Rect. Bar	QQA-200/11	0.5	4	35.25	1	7.1
X	7075-T6511 Rect. Bar	QQA-200/11	0.5	4	24	1	4.8
X	7075-T6511 Rect. Bar	QQA-200/11	0.5	6	144	4	172.8
X	7075-T6511 Rect. Bar	QQA-200/11	0.5	6	83.5	1	25.1
X	7075-T6511 Rect. Bar	QQA-200/11	0.5	1.625	48	1	3.9
X	7075-T6511 Rect. Bar	QQA-200/11	0.75	2.5	71.875	1	13.5
X	7075-T6511 Rect. Bar	QQA-200/11	0.75	6	40.5	1	18.2
X	7075-T6511 Rect. Bar	QQA-200/11	0.75	2.5	35.75	1	6.7
X	7075-T6511 Rect. Bar	QQA-200/11	1	2	12	1	2.4
X	7075-T6511 Rect. Bar	QQA-200/11	1	3	11.75	1	3.5
X	7075-T6511 Rect. Bar	QQA-200/11	1	1.5	144	13	280.8
X	7075-T6511 Rect. Bar	QQA-200/11	1	1.5	144	3	62.8
	7075-T6511 Sq. Bar	QQA-200/11	1	1	144.25	1	14.4
X	7075-T6511 Rect. Bar	QQA-200/11	1	2.5	41.5	1	10.4
X	7075-T6511 Rect. Bar	QQA-200/11	1	1.5	17.75	1	2.7
	7075-T6511 Sq. Bar	QQA-200/11	1	1	48	1	4.8
X	7075-T6511 Sq. Bar	QQA-200/11	1	1	35.875	1	3.6
X	7075-T6511 Rect. Bar	QQA-200/11	1	1.5	144	21	453.6
X	7075-T6511 Rect. Bar	QQA-200/11	1	1.5	36	1	5.4
X	7075-T6511 Sq. Bar	QQA-200/11	1.25	7	32.75	1	28.7
X	7075-T6511 Sq. Bar	QQA-200/11	1.25	7	48	1	42.0
X	7075-T651 Rect. Bar	QQA-200/11	1.375	0.875	72	1	8.7
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	1.5	11.9375	2	5.4
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	3	47.75	1	129.6
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	3	48	1	129.6
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	3	16.5	1	10.6
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	3	144	1	194.4
X	7075-T6 SQ BAR	QQA-200/11	1.5	1.5	47.25	1	10.7
X	7075-T651 Rect. Bar	QQA-200/11	1.5	2	48	1	14.4
	7075-T6511 Rect. Bar	QQA-200/11	1.5	3.25	52	1	25.4
X	7075-T6511 Rect. Bar	QQA-200/11	1.5	3.125	17	1	8.0
X	7075-T6511 Rect. Bar	QQA-200/11	2	2.5	11.5	1	5.8
X	7075-T6511 Rect. Bar	QQA-200/11	2.875	6	72	1	124.0
X	7075-T6511 Rect. Bar	QQA-200/11	2.75	1.375	144	1	54.5
	7075-T6511 Rect bar ( mach. from 3")	QQA-200/11	2.75	1.375	144	1	54.4
X	7075-T6511 Rect. Bar	QQA-200/11	3	4	47	1	56.4
X	7075-T6511 Rect. Bar	QQA-200/11	3	4	71.375	1	85.6
	7075-T6511 Rect bar ( mach.from 3")	QQA-200/11	1.625	1.75	144	1	40.9

X	7075-T6511 Rect. Bar	QQA-200/11	3	4	144	3	518.4
X	7075-T651 Rect. Bar	QQA-200/11	3.5	4	51.75	10	724.5
X	7075-T6511 Rect. Bar	QQA-200/11	4	6	11.75	1	173.0
X	7075-T7351 Rd. Bar	QQA-225/9	0.625		16.5	1	0.5
X	7075-T7351 Rd. Bar	QQA-225/9	0.625		48	1	1.5
X	7075-T7351 Rd. Bar	QQA-225/9	0.75		11.5	1	1.0
X	7075-T7351 Rd. Bar	QQA-225/9	1.25	1.75	23.625	1	5.2
X	7075-T7351 Rd. Bar	QQA-225/9	1.25		11.25	1	1.4
X	7075-T7351 Rd. Bar	QQA-225/9	1.75		23.875	1	5.8
X	7075-T7351 Rd. Bar	QQA-225/9	1.75		24	1	5.8
X	7075-T73511 Rd. Bar	QQA-200/11	0.625		47.5	1	1.5
X	7075-T7351 Rd. Bar	QQA-200/11	0.75		24	1	1.0
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		46.5	1	2.1
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		36	1	1.5
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		12	1	0.5
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		24	1	1.1
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		108	1	4.8
X	7075-T73511 Rd. Bar	QQA-200/11	0.75		96	1	4.3
X	7075-T73511 Rd. Bar	QQA-200/11	1	2	17.25	2	2.7
X	7075-T73511 Rd. Bar	QQA-200/11	1	2	86.912	1	6.9
X	7075-T73511 Rd. Bar	QQA-200/11	1.25		71.625	1	8.8
X	7075-T73511 Rd. Bar	QQA-200/11	1.25		35	1	4.3
X	7075-T73511 Rd. Bar	QQA-200/11	1.5		68.5	1	12.2
X	7075-T73511 Rd. Bar	QQA-200/11	2		24	1	7.6
X	7075-T73511 Rd. Bar	QQA-200/11	2.5		8.13	1	4.0
X	7075-T73511 Rd. Bar	QQA-200/11	2.5		5.38	1	2.7
X	7075-T73511 Rd. Bar	QQA-200/11	2.5		23.125	1	11.4
X	7075-T73511 Rd. Bar	QQA-200/11	4		9.25	1	11.7
X	7075-T73511 Rd. Bar	QQA-200/11	5.5		9.25	1	22.1
X	7075-T73511 Rd. Bar	QQA-200/11	5.5		9.5	14	317.0
X	7075-T73511 Rd. Bar	QQA-200/11	5.5		4.75	1	11.4

X	7075-T73511 Rd. Bar	QQA-200/11	6.5		20.875	1	69.6
X	7075-T7351 Rect. Bar	QQA-225/9	0.5	3	11.5	1	1.7
X	7075-T7351 Rect. Bar	QQA-225/9	0.5	3	32.75	1	4.9
X	7075-T7351 Rect. Bar	QQA-225/9	0.75	1	59.875	2	8.9
X	7075-T7351 Rect. Bar	QQA-225/9	1	3	11	1	3.3
X	7075-T7351 Rect. Bar	QQA-225/9	1	1.5	12	1	1.8
X	7075-T7351 Rect. Bar	QQA-225/9	1	1.75	59.75	1	20.9
X	7075-T7351 Rect. Bar	QQA-225/9	1	1.5	15	1	2.3
X	7075-T7351 Rect. Bar	QQA-225/9	5	5	9.625	1	19.0
X	7075-T7351 Rect. Bar	QQA-225/9	5	4	11	1	54
X	7075-T7351 Rect. Bar	QQA-225/9	5	6	7.125	1	21.3
X	7075-T7351 Square Bar	QQA-225/9	5	5	2.25	1	270.0
X	7075-T7351 Square Bar	QQA-225/9	5	5	6.25	1	270.0
X	7075-T7351 Square Bar	QQA-225/9	5	5	79.375	1	270.0
X	7075-T73511 Rect Bar	QQA-200/11	0.312	4	71.625	1	8.9
X	7075-T73511 Rect Bar	QQA-200/11	0.5	6	35.75	1	10.7
X	7075-T73511 Rect Bar	QQA-200/11	0.5	6	23.75	1	7.1
X	7075-T73511 Rect Bar	QQA-200/11	0.5	6	17.875	1	5.4
X	7075-T73511 Rect Bar	QQA-200/11	0.5	3.24	8	1	1.3
X	7075-T73511 Rect Bar	QQA-200/11	0.5	6	47.875	1	14.4
X	7075-T73511 Rect Bar	QQA-200/11	0.5	1.75	35.5	1	3.1
X	7075-T73511 Rect Bar	QQA-200/11	0.75	1.5	27.5	1	3.1
X	7075-T73511 Rect Bar	QQA-200/11	0.75	2	5	3	2.3
X	7075-T73511 Rect Bar	QQA-200/11	1	4	23.75	1	9.5
X	7075-T73511 Rect Bar	QQA-200/11	1	2	75.875	1	15.1
X	7075-T73511 Rect Bar	QQA-200/11	1	5.25	19.5	1	10.2
X	7075-T73511 Rect Bar	QQA-200/11	1	5.25	83.5	1	43.8
X	7075-T73511 Rect Bar	QQA-200/11	1	5.25	144	1	75.6
X	7075-T73511 Rect Bar	QQA-200/11	1	1.75	36	1	6.3
X	7075-T73511 Rect Bar	QQA-200/11	1	2.5	35.5	1	8.9
X	7075-T73511 Rect Bar	QQA-200/11	1	3	48	1	14.4
X	7075-T73511 Rect Bar	QQA-200/11	1	8	35.75	1	28.6
X	7075-T73511 Rect Bar	QQA-200/11	1.25	8	23.5	1	23.5
X	7075-T73511 Rect Bar	QQA-200/11	1.25	3	24	1	9.0
X	7075-T73511 Rect Bar cut from 1.375 thk	QQA-200/11	1.25	1.312	71.9375	1	11.8

X	7075-T73511 Rect Bar	QQA-200/11	1.5	6	21	1	18.9
X	7075-T73511 Rect Bar	QQA-200/11	1.5	4	22	1	13.2
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	1.5	1.5	35.6875	1	8.0
X	7075-T73511 Rect Bar	QQA-200/11	1.5	2	16.5	3	14.9
X	7075-T73511 Rect Bar	QQA-200/11	1.5	1.5	96.5	1	21.7
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	1.75	1.75	47.9375	1	14.7
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	1.75	1.75	144	1	132.3
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	2	2	60	1	24.0
X	7075-T73511 Rect Bar	QQA-200/11	2	2	35.875	1	14.4
X	7075-T73511 Rect Bar	QQA-200/11	2	1.6875	84	1	28.4
X	7075-T73511 Rect Bar	QQA-200/11	2	1.5	36	1	10.8
	7075-T73511 Rect Bar	QQA-200/11	2	3	23.5	1	14.1
X	7075-T73511 Rect Bar	QQA-200/11	2.5	3	12.375	1	9.3
	7075-T73511 Rect Bar - Consignment	QQA-200/11	3	4	72.125	15	1298.2
	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	3	3	9.5	1	8.6
	7075-T73511 Rect Bar	QQA-200/11	4	6	7.63	1	18.3
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	5	5	72	1	180.0
X	7075-T73511 <b>Sq. Bar</b>	QQA-200/11	5	5	60	1	150.0
X	356.1 ALUM. INGOT Rect Bar	CAST ALUM.	1.3125	4.3125	6.625	1	3.7